



Articulated arm for OKKIO camera with pole application,45-50 mm diameter

3 joints articulated arm for OKKIO camera with pole mounting, 45-50mm diameter, compatible with standard commercial cameras weighing up to 500 grams.

Available

SKU: OF933GA50

Categories: Configurations

Description

3 joints articulated arm for OKKIO camera with pole mounting, 45-50mm diameter.

Effortlessly Capture Photos and Videos

Tecnomed Italia has created a **flexible arm system** designed to hold OKKIO or other compatible cameras alongside the FALKOLED illuminator, positioning them at an ideal distance of 300-500 mm from the patient's mouth. The system is aligned with the dentist's line of sight during procedures.

This **adaptable setup** enables the capture of **clear images** and **steady video recordings**, all while eliminating shadows. Previously, documenting procedures required the help of an assistant or frequent pauses. Now, with the OKKIO arm, you can handle everything **on your own**, seamlessly, without interruptions.

The OKKIO arm's versatility also complements the use of the **FALKO visor**, which improves hand-eye coordination during treatments, helping to reduce motion sickness and ensuring better posture.

It can be easily configured to meet specific **operational demands** and fit the room's technical layout. A dedicated adapter makes it compatible with standard commercial cameras weighing up to 500 grams.

3 joints articulated arm for OKKIO camera with pole mounting.