



## Articulated arm for OKKIO camera with pole application, 45-50 mm diameter

3 joints articulated arm for OKKIO camera with pole mounting, 45-50mm diameter, compatible with standard commercial cameras weighing up to 500 grams.

**Shipping expected in approximately 10 days**

**SKU:** OF933GA50

**Categories:** Configurations

### Description

---

**3-joint articulated arm for the OKKIO medical camera with lamp pole mounting Ø 45–50mm**, designed to ensure **stable, precise and functional positioning** of the camera during dental procedures. The system allows the **OKKIO medical camera** to be oriented following the clinician's natural line of sight, making it easy to capture **photos and videos** without interfering with clinical workflow.

Thanks to its articulated structure, the camera can be positioned flexibly and maintained at the correct distance from the operating area, ensuring **sharp images and stable recordings**. The **lamp pole mounting support** provides a **practical and reliable solution** for clinical documentation, allowing professionals to work **independently**, without interruptions and without the need for a dedicated operator.

An ideal choice for keeping the workstation **clean, professional and well organized**, improving daily efficiency and the overall quality of visual documentation. The articulated arm can be configured according to operational needs and room characteristics. Thanks to a **dedicated adapter (not included)**, it is also compatible with **other cameras featuring a standard photographic mount**, supporting a maximum weight of **500g**.