



Printed on 31/05/2025

<https://shop.tecnomeditalia.com/en/product/aspiratore-anello-semiumido-1-riunito-con-centralina/>



VAX suction system, 1 dental unit, semi-wet loop, with control unit

Dental suction unit VAX, 300-450W 230V, 1 dental unit, wet loop, control unit

1.459,61 €

Available

SKU: DEJ300

Categories: Vax wet ring

Description

Suction system 1 dental unit semi-wet loop, with control unit.

VAX semi-wet Ring Suction Systems: Efficiency and Value for Your Dental Practice

VAX wet ring aspiration systems offer a reliable, economical, and high-performance solution for dental practices of all sizes. Designed to provide continuous and powerful suction, VAX systems are an excellent choice for those seeking a good balance between quality and cost without sacrificing operational efficiency.

Features of VAX semi-wet Ring Aspiration Systems:

- **Efficient and Reliable Suction:** VAX systems ensure consistent suction power during daily use, maintaining a clean and safe working environment.
- **Robust and Easy to Manage Design:** Built with high-quality materials, VAX systems are designed for durability, offering easy installation and minimal maintenance.
- **Value for Money:** VAX combines reliable performance with a competitive price, making it ideal for dental practices looking for a functional and cost-effective solution.

Why Choose VAX semi-wet Ring Aspiration Systems?

Despite its competitive price, VAX delivers suction technology that meets the needs of dental practices, enhancing efficiency without compromise. It is a practical solution for those seeking durable and dependable suction quality.

Opt for VAX semi-wet ring aspiration systems for efficient suction and a smart investment. With VAX, you bring a quality product to your practice that delivers on its promise, at an accessible price.

Technical features Suction system 1 dental unit semi-wet loop:

Type	semi-wet
Dental units served	1 at 100%
Control unit	yes

Own cabinet	lower
Water drain	continuous drain
Noise level (db)	?56
Amalgam recovery	optional
Power (Watt)	450
Vacuum (mBar)	120
Flow rate (l/min)	1100
Power supply (Volt/Hz)	AC230/50
Weight (Kg)	22
Dimensions (l x p x h) mm	370 x 310 x 580
Warranty (months)	24
Certification	CE MDR