



Printed on 14/06/2025

<https://shop.tecnomeditalia.com/en/product/aspiratore-anello-umido-1-4-riuniti-smart-control-tecnology-dynamic/>

## VAX suction system, 1-4 dental units, wet loop, with smart control



Dental suction unit VAX, 1200 1450W 230V, 1 to 4 dental units, wet loop, smart control technology.

**Available**

**SKU:** DEJ1200IN

**Categories:** Vax wet ring

### Description

Suction system 1-4 dental unit, wet loop, with smart control technology.

### VAX Wet Ring Suction Systems: Efficiency and Value for Your Dental Practice

VAX wet ring aspiration systems offer a reliable, economical, and high-performance solution for dental practices of all sizes. Designed to provide continuous and powerful suction, VAX systems are an excellent choice for those seeking a good balance between quality and cost without sacrificing operational efficiency.

#### Features of VAX Wet Ring Aspiration Systems:

- **Efficient and Reliable Suction:** VAX systems ensure consistent suction power during daily use, maintaining a clean and safe working environment.
- **Robust and Easy to Manage Design:** Built with high-quality materials, VAX systems are designed for durability, offering easy installation and minimal maintenance.
- **Value for Money:** VAX combines reliable performance with a competitive price, making it ideal for dental practices looking for a functional and cost-effective solution.

#### Why Choose VAX Wet Ring Aspiration Systems?

Despite its competitive price, VAX delivers suction technology that meets the needs of dental practices, enhancing efficiency without compromise. It is a practical solution for those seeking durable and dependable suction quality.

Opt for VAX wet ring aspiration systems for efficient suction and a smart investment. With VAX, you bring a quality product to your practice that delivers on its promise at an accessible price.

#### Technical features Suction system 1-4 dental unit:

Type	water-ring
------	------------

Dental units served	1/4
Control unit	yes-inverter
Own cabinet	No
Water drain	centrifugal
Noise level (db)	?57
Amalgam recovery	optional
Power (Watt)	1450
Vacuum (mBar)	180
Flow rate (l/min)	1800
Power supply (Volt/Hz)	AC230/50
Weight (Kg)	42
Dimensions (lpxh)mm	580 x 450 x 530
Warranty (months)	24
Certification	CE MDR