

Bearing, high speed,4x7x2 ceramic, torlon,200.000 RPM,Myonic



Available

SKU: SB200W

Categories: Internal diameter 4-5

Description

Low speed handpiece bearing, 4x7x2mm, Myonic smooth type, spare part for dental handpieces, with torlon cage and ceramic balls.

Handpiece compatibility

- Ivory SL415C/L, S/N < 2201000: bur side and push side
- Ivory SL415C/L, S/N > 2201001: bur side and push side
- Mk-Dent LS2115L: bur side and push side
- Bien-Air CA 1:5 L: bur side and push side
- Sirona T1 Line C200/L – T2 Line A 200/L – T2 Line A170/L – T3 Line E200/L, Gear 13 Z Ø 9.7mm: bur side and push side
- W&H WE-99 A/LED G: bur side and push side
- NSK S-Max M95/L: bur side and push side
- NSK S-Max M95/L, outer diameter of the bearing push side 6.5mm: bur side and push side
- NSK Ti-Max T195/L1 – T195/L2: bur side and push side
- NSK Ti-Max X95/L: bur side and push side
- NSK Ti-Max Z95/L, outer diameter of the bearing push side 7mm: push side

Technical features

- Dimensions: height 2mm, internal diameter 4mm, external diameter 7mm
- Smooth bearing
- Torlon cage
- Ceramic balls
- Angular contact
- Myonic brand
- 12-month warranty