


Bearing, low speed, 3,5X6,5X2 KK for Kavo M25L – Rear, 200.000 RPM



Bearing for low speed handpiece, dimensions 3.5x6.5x2mm, smooth, steel cage, ceramic balls, 200.000 rpm, Tecnomed Italia brand, compatible with KaVo M25L.

Available

SKU: SB25MR

Categories: Internal diameter 2-3

Description

Low speed handpiece bearing, 3.5x6.5x2mm, smooth type, Tecnomed Italia, spare part for dental handpieces, with steel cage and ceramic balls.

Handpiece compatibility

- KaVo M25L Contra-angle red ring: push side

Technical features

- Dimensions: height 2mm, internal diameter 3.5mm, external diameter 6.5mm
- Smooth bearing
- Steel cage
- Ceramic balls
- Radial contact
- 200.000 rpm
- Tecnomed Italia brand
- 12-month warranty