



BL Iso C Sirona micromotor hose comp., 1370mm, 3,88kohm,for Teneo,Sinius

Micromotor hose, 1370mm, Sirona BL ISO C Motor - Teneo, Sinius, Intego, Intego Pro compatible, 2 kohm, swivel, light grey colour.

Estimated shipping in 15 days

SKU: PC235SBIC

Categories: Micromotors

Description

1370mm micromotor hose compatible with Sirona BL ISO C Motor (Teneo, Sinius, Intego, Intego Pro), with rotation and 3.88kohm resistance. Light grey color.