



OKKIO articulated arm with 3 joints, for OKKIO cameras, white colour

Articulated arm made of aluminium, with 3 articulated ball joints and cable hiding system, for OKKIO camera (HDMI, Micro USB)

Available

SKU: FK933C

Categories: OKKIO Mounts

Description

3-joint articulated arm for OKKIO camera, made of **aluminium**, featuring **three articulated ball joints** and an **integrated internal cable management system**, with cables routed **inside the arm** for a clean, professional installation.

Designed for use with **OKKIO HDMI and Micro USB cameras**.

The articulated arm system is designed to position OKKIO cameras, or other compatible cameras, in combination with the **FALKOLED illuminator**, at an optimal distance of **300–500mm from the oral cavity**, following the clinician's natural line of sight during dental procedures.

This exceptional flexibility allows **high-quality images and stable video recordings**, without shadows or visual obstructions. In the past, documenting a procedure required an additional operator or interruptions to clinical activity; today, thanks to the OKKIO arm, these operations can be carried out **independently**, without interruptions and without obstacles.

The versatility of the OKKIO arm also makes it perfectly suitable for use with the **FALKO visor**, providing a viewing experience that supports eye–hand coordination during procedures and helps prevent **motion sickness and postural strain**.

The articulated arm can be configured according to operational requirements and room characteristics. Thanks to a **dedicated adapter**, it is also compatible with **commercial cameras featuring a standard photographic mount**, supporting a maximum weight of **500g**.

Multiple mounting options: wall-mounted, tabletop, clamp-mounted, dental unit headrest (*mounting supports sold separately*).