



## Articulated arm for OKKIO camera with wall application

Articulated arm for OKKIO camera made of aluminium with 3 articulated ball joints, cable hiding system. With 70 cm extension arm (cod. FK935B) and wall support (cod FK934P).

**Available**

**SKU:** OF933PA

**Categories:** Configurations

### Description

---

#### Articulated arm for OKKIO with wall application – Effortlessly Capture Photos and Videos

Tecnomed Italia has created a **flexible arm system** designed to hold OKKIO or other compatible cameras alongside the FALKOLED illuminator, positioning them at an ideal distance of 300-500 mm from the patient's mouth. The system is aligned with the dentist's line of sight during procedures.

The **Articulated arm for OKKIO with wall application** enables the capture of **clear images** and **steady video recordings**, all while eliminating shadows. Previously, documenting procedures required the help of an assistant or frequent pauses. Now, with the OKKIO arm, you can handle everything **on your own**, seamlessly, without interruptions.

It can be easily configured to meet specific **operational demands** and fit the room's technical layout. A dedicated adapter (not included) makes it compatible with standard commercial cameras weighing up to 500 grams.