



Articulated arm for OKKIO camera with wall application

Articulated arm for OKKIO camera made of aluminium with 3 articulated ball joints, cable hiding system. With 70 cm extension arm (cod. FK935B) and wall support (cod FK934P).

Available on request

SKU: OF933PA

Categories: Configurations

Description

3-joint articulated arm for the OKKIO medical camera with white wall-mounted application, including a **70cm extended arm** and **wall mounting bracket**, designed to ensure **stable, precise and functional positioning** of the camera during dental procedures.

The system allows the **OKKIO medical camera** to be oriented following the clinician's natural line of sight, making it easy to capture **photos and videos** without interfering with clinical workflow.

Thanks to its articulated structure and extended arm, the camera can be positioned flexibly and maintained at the correct distance from the operating area, ensuring **sharp images and stable recordings**. The wall-mounted support provides a **practical and reliable solution** for clinical documentation, ideal for optimizing space and allowing professionals to work **independently**, without interruptions and without the need for a dedicated operator.

An ideal choice for keeping the workstation **clean, professional and well organized**, improving daily efficiency and the overall quality of visual documentation. The articulated arm can be configured according to operational needs and room characteristics. Thanks to a **dedicated adapter (not included)**, it is also compatible with **other cameras featuring a standard photographic mount**, supporting a maximum weight of **500g**.