



## Articulated arm for OKKIO camera with clamp

Articulated arm for OKKIO camera made of aluminium with 3 articulated ball joints, cable hiding system and clamp support included (Cod. FK937M). For OKKIO HDMI and OKKIO Micro USB, color white.

**Available**

**SKU:** OF933MO

**Categories:** Configurations

### Description

---

#### Articulated arm for OKKIO camera with clamp – Effortlessly Capture Photos and Videos

Tecnomed Italia has created a **flexible arm system** designed to hold OKKIO or other compatible cameras alongside the FALKOLED illuminator, positioning them at an ideal distance of 300-500 mm from the patient's mouth. The system is aligned with the dentist's line of sight during procedures.

The articulated arm for OKKIO camera with clamp enables the capture of **clear images** and **steady video recordings**, all while eliminating shadows. Previously, documenting procedures required the help of an assistant or frequent pauses. Now, with the OKKIO arm, you can handle everything **on your own**, seamlessly, without interruptions.

It can be easily configured to meet specific **operational demands** and fit the room's technical layout. A dedicated adapter makes it compatible with standard commercial cameras weighing up to 500 grams.

White Clamp support included (Cod. FK937M)