



## Articulated arm for OKKIO camera with clamp

Articulated arm for OKKIO camera made of aluminium with 3 articulated ball joints, cable hiding system and clamp support included (Cod. FK937M). For OKKIO HDMI and OKKIO Micro USB, color white.

**Available**

**SKU:** OF933MO

**Categories:** Configurations

### Description

---

**3-joint articulated arm for the OKKIO medical camera with clamp support**, designed to ensure **stable, precise and functional positioning** of the camera during dental procedures.

The system allows the **OKKIO medical camera** to be oriented following the clinician's natural line of sight, making it easy to capture **photos and videos** without interfering with clinical workflow.

Thanks to its articulated structure, the camera can be positioned flexibly and maintained at the correct distance from the operating area, ensuring **sharp images and stable recordings**. The clamp support provides a **practical and reliable solution** for clinical documentation, allowing professionals to work **independently**, without interruptions and without the need for a dedicated operator.

An ideal choice for keeping the workstation **clean, professional and well organized**, improving daily efficiency and the overall quality of visual documentation. The articulated arm can be configured according to operational needs and room characteristics. Thanks to a **dedicated adapter (not included)**, it is also compatible with **other cameras featuring a standard photographic mount**, supporting a maximum weight of **500g**.