



## Ceiling-mounting for Esa Line, pole 1450mm

Ceiling-mounting for Esalight - Esalight2 and/or Esacam, pole 1450mm for ceiling from 2.7 to 3 metres, 230Vac/12-24Vac

**Available on request**

**SKU:** DE6.3133

**Categories:** Light Mounting

### Description

---

Ceiling-mounting for EsaLine pole 1450mm

Dental light ceiling mounts are suitable for all types of lights with a 35 mm diameter unit pin.

The output power supply of 24vac makes the product compatible with most of the lights on the market.

They are suitable for mountings with high ceilings from 2700 mm to 3500 mm.