

Complete heads ENDOMATE NSK / ENDOSMMART MM18EN compatible



Complete heads NSK MP-F16R reducer / Dentsplay X-SMART PLUS 16:1 compatible, max Speed 20.000 rpm, push button.

Shipping expected in approximately 30 days

SKU: 110TM096

Categories: NSK

Description

Complete head compatible with ENDOMATE NSK ENDOSMART is a professional solution for endodontics, designed for users looking for a practical, reliable replacement part suitable for use with compatible **NSK** systems.

Designed for use with the **NSK MP-F16R reduction handpiece**, it helps keep endodontic instrumentation efficient and allows simple replacement when the head needs to be changed.

The **push-button bur locking system** makes the head practical and secure to use, allowing the instrument to be fixed easily during operating procedures.

With a maximum speed of **20.000rpm**, the head offers a configuration suitable for daily endodontic applications, supporting functionality and working continuity.

Technical features complete head compatible ENDOMATE NSK ENDOSMART.

Indications	endodontic
Ratio	1:1
Locking mechanism	Push Button
Head diameter (mm)	8.1
Head height (mm)	8.3
Bur diameter (mm)	CA/RA 2,35mm
Bur length (mm)	endo
Type of lubrication	Oil



Autoclave resistant	Yes, 135°C
Max Speed (rpm)	20.000
Packing weight appr. (g)	120
Certification	CE