



Complete heads ENDOMATE NSK / ENDOSMMART MM18EN compatible

Complete heads NSK MP-F16R reducer / Dentsplay X-SMART PLUS 16:1 compatible, max Speed 20.000 rpm, push button.

Estimated shipping in 30 days

SKU: 110TM096

Categories: NSK

Description

Complete head for Endo Mate NSK / Endo Smart.

Suitable for NSK MP-F16R reducer or Dentsplay X-SMART PLUS 16:1,

- ideal for endodontic and standard uses;
- Locking mechanism by Push Button;
- Max Speed 20.000 rpm.

Technical features Complete heads ENDOMATE NSK / ENDOSMART.

Indications	endodontic
Ratio	1:1
Locking mechanism	Push Button
Head diameter (mm)	8.1
Head height (mm)	8.3
Bur diameter (mm)	CA/RA 2,35mm
Bur length (mm)	endo
Type of lubrication	Oil
Autoclave resistant	Yes, 135°C
Max Speed (rpm)	20.000
Packing weight appr. (g)	120



Certification	CE
---------------	----