



Printed on 30/05/2025

<https://shop.tecnomeditalia.com/en/product/conductivity-meter-lcd-with-water-stop-and-flow-switchbuiltin/>



## Conductivity meter lcd with water stop and flow switch,builtin.

Conductivity meter for automatic water quality check, it blocks dispensing in case the resins are no longer effective.

**467,81 €**

**Available**

**SKU:** DCV22LC

**Categories:** Water demineralisers

### Description

---

Conductivity meter lcd with water stop and flow switch.

The demineralizer can be equipped with a conductivity meter that automatically detects water quality and blocks the dispensing in case the resins are no longer effective. Once the resins are exhausted they can be easily replaced by the operators.

If you want to constantly monitor the quality of the produced demineralized water and block the flow in case it is poor quality, you can integrate the conductivity meter with LCD display to the demineralizer.

Through the dip switch placed inside the panel you can set the maximum threshold of the desired micro siemens from 10 to 400 microns (factory settings 30 microns). An electrovalve blocks the flow of outgoing water if it exceeds the set value.