



## Dry air compressor, 1 unit, 70 l/min, without dryer

Tecnomed Silent Line dry air compressor for 1 dental unit, 25l tank, air output 70 l/min, without dryer

**Available**

**SKU:** 100TOV

**Categories:** Without Dryer

### Description

---

#### Medical Air Compressor 1 Unit – Silent, Efficient and Reliable for Dental Clinics

The **Tecnomed Silent** medical air compressor for 1 unit is designed to supply clean, dry and safe compressed air for one dental unit. It ensures consistent performance and a quiet working environment, perfectly suited to the needs of modern dental practices and medical facilities.

#### Silent and Comfortable Operation

The soundproofed system guarantees exceptionally quiet performance, reducing noise levels and improving the acoustic comfort of the workspace. This creates a calm and professional environment, enhancing operator focus and ensuring a more relaxed experience for patients.

#### Clean Air and Oil-Free Technology

The **completely oil-free head**, compliant with medical and dental standards, delivers pure and uncontaminated compressed air. This feature reduces maintenance and ensures maximum hygiene and reliability during all clinical applications.

#### Durability and Long-Term Resistance

The tank undergoes **hard anodising** and features an **internal anti-corrosion coating**, which increase strength and service life, even under intensive operating conditions.

#### Reliable Choice for Modern Practices



Silent, efficient and long-lasting, the **Tecnomed Silent** system provides a steady flow of clean air for dental surgeries and clinics that demand consistent performance and full compliance with medical quality standards.

**Technical features Medical Dry-air compressor 1 dental unit 70l/min.**

Dental units served	1
Air flow	70 liters/minutes
Aspirated volume	115 liters
Tank capability	25 liters
Oil less	•
Air dryer	No
Own cabinet	
Twin cylinder stages	1
Power	550 Watt
Noise level	52 db
Operating Pressure	5,5-8 Bar
Power supply	220/240V-50/60 Hz
Weight	24 kg
Dimensions (W x L x H)	400 x 400 x 530 mm
Warranty	24 months
Certification	CE