




Printed on 31/05/2025

<https://shop.tecnomeditalia.com/en/product/dry-air-compressor-3-units-195-l-min-with-dryer/>



Dry air compressor, 3 units, 195 l/min, with dryer

Tecnomed Silent Line dry air compressor for 3 treatment units, 60l tank, air output 195 l/min, with dryer

3.128,65 €

Available on request

SKU: 360TOVEN

Categories: With air dryer

Description

Medical Dry-air compressor 3 dental units with dryer.

Tecnomed Silent Compressors – Unmatched Silence and Performance for Your Practice.

The Tecnomed Silent Dry Compressor is the perfect choice for dental practices and clinics that require a silent solution for up to 3 dental units. Engineered to deliver a serene working environment, high efficiency, and long-lasting durability, this compressor is designed with your practice's needs in mind.

Key Features:

- **Exceptional Quietness:** The Tecnomed Silent Compressor operates with minimal noise, creating a more comfortable work environment.
- **Optimal Performance:** Equipped with a durable copper motor and oil-free piston, this compressor ensures high efficiency and reduced heat dissipation.
- **Superior Durability:** With a hard anodized process and anti-corrosion internal coating, the compressor is built to last.
- **Advanced Dryer:** The integrated dryer with triple filtration removes moisture and impurities, guaranteeing clean, high-quality air.

Why Choose Tecnomed Silent Compressors?

Tecnomed Silent Compressors are ideal for those seeking top-notch quietness and performance. Featuring advanced technology, these compressors ensure a peaceful and comfortable working environment while maintaining high standards of efficiency and durability. They provide purified air and long operational life, making them the optimal choice for dental practices and clinics that demand quality and reliability without compromise.

Technical features Medical Dry-air compressor 3 dental units with dryer.

Dental units served	3
---------------------	---

Air flow	195 liters/minutes
Aspirated volume	304 liters
Tank capability	60 liters
Oil less	•
Air dryer	•
Own cabinet	
Twin cylinder stages	2
Power	1500 Watt
Noise level	53 db
Power supply	220/240V-50/60 Hz
Weight	37 kg
Dimensions (W x L x H)	715 x 500 x 735 mm
Warranty	24 months
Certification	CE