



Dry air compressor, 3 units, 205 l/min without dryer

Tecnomed Silent Line dry air compressor for 3 treatment units, 60l tank, air output 205 l/min, without dryer

Estimated shipping in 60 days

SKU: 360TOV

Categories: Without Dryer

Description

Medical Air Compressor for 3 Units – Silent, Efficient and Reliable for Dental Clinics

The **Tecnomed Silent** medical air compressor for 3 units is designed to supply clean, dry and safe compressed air for up to 3 dental units. It ensures consistent performance and a quiet working environment, perfectly suited to the needs of modern dental practices and medical facilities.

Silent and Comfortable Operation

The soundproofed system guarantees exceptionally quiet performance, reducing noise levels and improving the acoustic comfort of the workspace. This creates a calm and professional environment, enhancing operator focus and ensuring a more relaxed experience for patients.

Clean Air and Oil-Free Technology

The **completely oil-free head**, compliant with medical and dental standards, delivers pure and uncontaminated compressed air. This feature reduces maintenance and ensures maximum hygiene and reliability during all clinical applications.

Durability and Long-Term Resistance

The tank undergoes **hard anodising** and features an **internal anti-corrosion coating**, which increase strength and service life, even under intensive operating conditions.

Reliable Choice for Modern Practices



Silent, efficient and long-lasting, the **Tecnomed Silent** system provides a steady flow of clean air for dental surgeries and clinics that demand consistent performance and full compliance with medical quality standards.

Technical features Medical Dry-air compressor 3 dental units.

Dental units served	3
Air flow	195 liters/minutes
Aspirated volume	304 liters
Tank capability	60 liters
Oil less	•
Air dryer	No
Own cabinet	
Twin cylinder stages	2
Power	1500 Watt
Noise level	52 db
Operating Pressure	5,5-8 Bar
Power supply	220/240V-50/60 Hz
Weight	51 kg
Dimensions (W x L x H)	715 x 367 x 735 mm
Warranty	24 months
Certification	CE