



Dry air compressor for 1+1 dental units, 95l/min, without dryer

Tecnomed Silent Line dry air compressor for 1+1 dental units, 38l tank, air output 95 l/min, without dryer

Available

SKU: 150TOV

Categories: Without Dryer

Description

Medical Air Compressor 1+1 Units – Quiet, Efficient and Reliable for Dental Clinics

The **Tecnomed Silent medical air compressor 1+1 units** delivers clean, dry and reliable compressed air for one or two dental units. Designed for professional environments, it combines silent operation, steady performance and long-term dependability — making it ideal for modern dental surgeries and medical practices.

Whisper-Quiet Operation

The advanced soundproofing system ensures extremely quiet performance, creating a calm and comfortable working atmosphere. Lower noise levels help maintain staff focus and provide patients with a more relaxing experience during treatment.

Oil-Free and Hygienic Air Supply

Equipped with a **fully oil-free head**, the compressor provides pure, uncontaminated air that meets strict medical and dental standards. This technology eliminates the risk of oil residues, minimises maintenance and guarantees optimal hygiene for all clinical applications.

Built to Last

A **hard-anodised tank** with an **internal anti-corrosion coating** offers maximum protection against wear and moisture. These features ensure consistent performance and durability, even under intensive daily use.

Dependable Performance for Modern Practices



Quiet, efficient and easy to maintain, the **Tecnomed Silent** compressor ensures a constant supply of high-quality air — the reliable choice for dental professionals who demand safety, precision and consistency in every procedure.

Technical features Medical dry-air compressor 1+1 dental unit.

Dental units served	1+1
Air flow	95 liters/minutes
Aspirated volume	152 liters
Tank capability	38 liters
Oil less	•
Air dryer	•
Own cabinet	
Twin cylinder stages	1
Power	750 Watt
Noise level	53 db
Operating Pressure	5,5-8 Bar
Power supply	220/240V-50/60 Hz
Weight	28 kg
Dimensions (W x L x H)	400 x 400 x 680 mm
Warranty	24 months
Certification	CE