



Printed on 07/06/2025

<https://shop.tecnomeditalia.com/en/product/dry-air-compressor-for-1+1-dental-units-95l-min-with-dryer/>



Dry air compressor for 1+1 dental units, 95l/min, with dryer

Tecnomed Silent Line dry air compressor for 1+1 dental units, 38l tank, air output 95 l/min, with dryer

2.066,05 €

Available

SKU: 150TOVEN

Categories: With air dryer

Description

Medical dry-air compressor 1+1 dental units with dryer.

Tecnomed Silent Compressors – Unmatched Silence and Performance for Your Practice

The Tecnomed Silent Dry Compressor is the perfect choice for dental practices and clinics that require a silent solution for up to 1+1 dental units. Engineered to deliver a serene working environment, high efficiency, and long-lasting durability, this compressor is designed with your practice's needs in mind.

Key Features:

- **Exceptional Quietness:** The Tecnomed Silent Compressor operates with minimal noise, creating a more comfortable work environment.
- **Optimal Performance:** Equipped with a durable copper motor and oil-free piston, this compressor ensures high efficiency and reduced heat dissipation.
- **Superior Durability:** With a hard anodized process and anti-corrosion internal coating, the compressor is built to last.
- **Advanced Dryer:** The integrated dryer with triple filtration removes moisture and impurities, guaranteeing clean, high-quality air.

Why Choose Tecnomed Silent Compressors?

Tecnomed Silent Compressors are ideal for those seeking top-notch quietness and performance. Featuring advanced technology, these compressors ensure a peaceful and comfortable working environment while maintaining high standards of efficiency and durability. They provide purified air and long operational life, making them the optimal choice for dental practices and clinics that demand quality and reliability without compromise.

Technical features Medical dry-air compressor 1+1 dental units with dryer

Dental units served	1+1
---------------------	-----

Air flow	95 liters/minutes
Aspirated volume	152 liters
Tank capability	38 liters
Oil less	•
Air dryer	•
Own cabinet	
Twin cylinder stages	1
Power	750 Watt
Noise level	53 db
Power supply	220/240V-50/60 Hz
Weight	37 kg
Dimensions (W x L x H)	430 x 400 x 660 mm
Warranty	24 months
Certification	CE