



## EL1 Sirona micromotor hose compatible,1350mm,30,4kohm,for Sirona c8,c8+

Micromotor hose, 1350mm, Sirona EL1, C8, C8+, Pro Feel compatible, 30,4 kohm

**Shipping expected in approximately 30 days**

**SKU:** PC224S/2N

**Categories:** Micromotors

### Description

---

Hose for micromotor compatible with Sirona EL1, C8, C8+, Pro Feel. Length 1350mm, resistance 30.4kohm. Designed for accurate and efficient replacement.