



Printed on 31/05/2025

<https://shop.tecnomeditalia.com/en/product/esalight-operating-lamp-35000-lux/>



## Esalight operating lamp, 35,000 Lux

Esalight operating lamp, LED 35,000 Lux, colour RAL9003, 35mm plug

**994,36 €**

**Available on request**

**SKU:** DE6.20C

**Categories:** Operating lighting lamps

### Description

---

The stylish Esalight operating lamp 35.000 lux delivers excellent illumination thanks to its original 6 separate LED illumination system.

This light's perfect chromatic efficiency ensures clear white light throughout the field of illumination.

Advanced technology eliminates the risk of overheating, even after eight hours continuous use, and ensures an LED life of around 50,000 hours.

The projected light beam illuminates the entire oral cavity without dazzling the patient and therefore guarantees maximum comfort.

### Technical features Esalight operating lamp with 35.000 lux

- Colour temperature: 5000~6000°K
- Spot dimensions: 80x165 mm
- Intensity: 5000 – 35000 Lux
- LED bulb lifespan: 50,000h
- Removable handles for quick cleaning
- Power Supply: 12 VAC  $\pm 10\%$  / 24 VAC  $\pm 10\%$ .
- Compliance with (UE) 2017/745 standards