



## Esalight2 operating lamp, 60,000 Lux, on stand

**Available on request**

**SKU:** DE6.3023ST

**Categories:** Dental Operating Lights

### Description

---

**Esalight2 operating lamp on stand, 60.000 lux, combines functional design with cutting edge technologies.**

**We give light to your needs:** have always the right amount of light for every treatment, thanks to a crisscross system of 6 or 12 LED technology light beams that cover an 100x200 light spot.

**Turn it on without touch it:** The sensor, positioned near the handle, lets you turn on, turn off and adjust the intensity of the light without touching the light itself, making it both practical and hygienic.

**Hygiene, the most important thing:** The handle can be detached and sterilized in an autoclave at 135° for quick and effective cleaning.

**Custom set-up.** The 35mm pin allows the Esa Line to be fitted on the posts of the most popular dental units and is compatible with Tecnomed's proposed ceiling mounting.

**Configuration on a mobile stand with wheels.**

#### Technical features Esalight2 operating lamp stand

- Colour temperature: 5000K\* +/-10%
- Colour rendering index (Ra): >95
- Spot dimensions: 100 x 200 mm
- Intensity: 8000 – 60000 Lux
- LED bulb lifespan: 50,000h



- Removable handle for quick cleaning
- Power Supply: 240/24 VAC
- Certification: 93/42/EEC
- Compliance with (UE) 2017/745 standards