



Esalight2 operating lamp, 60,000 Lux, on stand

Available on request

SKU: DE6.3023ST

Categories: Operating lighting lamps

Description

Esalight2 operating lamp on stand, 60.000 lux, combines functional design with cutting edge technologies.

We give light to your needs: have always the right amount of light for every treatment, thanks to a crisscross system of 6 or 12 LED technology light beams that cover an 100x200 light spot.

Turn it on without touch it: The sensor, positioned near the handle, lets you turn on, turn off and adjust the intensity of the light without touching the light itself, making it both practical and hygienic.

Hygiene, the most important thing: The handle can be detached and sterilized in an autoclave at 135° for quick and effective cleaning.

Custom set-up. The 35mm pin allows the Esa Line to be fitted on the posts of the most popular dental units and is compatible with Tecnomed's proposed ceiling mounting.

Configuration on a mobile stand with wheels.

Technical features Esalight2 operating lamp stand

- Colour temperature: 5000K* +/-10%
- Colour rendering index (Ra): >95
- Spot dimensions: 100 x 200 mm
- Intensity: 8000 – 60000 Lux
- LED bulb lifespan: 50,000h



- Removable handle for quick cleaning
- Power Supply: 240/24 VAC
- Certification: 93/42/EEC
- Compliance with (UE) 2017/745 standards