



## Esalight2 operating lamp, 60,000 Lux, on stand

## Available on request

SKU: DE6.3023ST

Categories: Dental Operating Lights

## **Description**

Esalight2 operating lamp on stand, 60.000 lux, combines functional design with cutting edge technologies.

We give light to your needs: have always the right amount of light for every treatment, thanks to a crisscross system of 6 or 12 LED technology light beams that cover an 100×200 light spot.

**Turn it on without touch it:** The sensor, positioned near the handle, lets you turn on, turn off and adjust the intensity of the light without touching the light itself, making it both practical and hygienic.

**Hygiene, the most important thing:** The handle can be detached and sterilized in an autoclave at 135° for quick and effective cleaning.

**Custom set-up.** The 35mm pin allows the Esa Line to be fitted on the posts of the most popular dental units and is compatible with Tecnomed's proposed ceiling mounting.

Configuration on a mobile stand with wheels.

## Technical features Esalight2 operating lamp stand

• Colour temperature: 5000K\* +/-10%

• Colour rendering index (Ra): >95

• Spot dimensions: 100 x 200 mm

• Intensity: 8000 - 60000 Lux

• LED bulb lifespan: 50,000h



• Removable handle for quick cleaning

• Power Supply: 240/24 VAC

• Certification: 93/42/EEC

• Compliance with (UE) 2017/745 standards