



FALKOLED Light 5700K°, 24000 LUX, jack connection, for OKKIO HDMI

LED illuminator designed for OKKIO HDMI cameras, round spotlight of 24,000 lux, 5700 K° color temperature, brightness adjustment via plug-in touchpad, powered by 12 VDC.

Available

SKU: IL901H

Categories: LED Illuminators

Description

FALKOLED Illuminator for OKKIO HDMI.

Cameras Lighting quality is essential for capturing high-quality photos and videos. The IL901H, specifically designed for OKKIO HDMI cameras, offers a round spotlight of 24,000 lux and a color temperature of 5700 K°, providing clear, shadow-free visibility, ideal for recording in clinical environments. The plug-in touchpad allows easy brightness adjustment, ensuring the light is always suited to the recording conditions.

High-quality lighting is crucial to avoid glare, shadows, and color distortions that could affect image quality. The IL901H ensures stable illumination, which is essential for medical procedures requiring visual precision.

Powered by 12 VDC, this illuminator provides the power necessary for professional, extended use, delivering excellent visual results in any situation.

Technical features:

- Specifically designed for OKKIO HDMI cameras.
- round spotlight with 24,000 lux brightness.
- 5700 K° color temperature for natural, stable light.
- On/off and brightness adjustment via plug-in touchpad.
- Powered by 12 VDC.
- Stable, even light for high-quality videos and photos in clinical environments.

Technical features FALKOLED Illuminator OKKIO HDMI

| | |
|-------------|------------|
| Model | IL901H |
| Application | OKKIO HDMI |



| | |
|----------------------------|------------------|
| LED Mount Type | SCREW 1/4-20 UNC |
| Anti-Polymerization Filter | / |
| Adjustable Intensity | TOUCHPAD |
| Maximum Intensity (LUX) | 24000 |
| Color Temperature (K) | 5700 |
| CRI | > 80 |
| Spot Shape | CIRCULAR |
| Spot Size at 250 mm | 8 CM |
| Power Connector | JACK 5.5 x 2.1mm |
| Power Supply | 12 VDC |
| Current Consumption (mA) | 500 |
| Cable Length (m) | / |
| Battery | / |
| Weight (g) | 10 |
| Dimensions (mm D x L) | 18 x 38 |