



Green Ivory Silk Line 2:1 fiber optic contra-angle, spray, comp. KaVo

Ivory Silk Line 2:1 green contra-angle with optical fibre, Intramatic coupling, internal spray, Kavo compatible head

Available

SKU: SL421L

Categories: Contra-Angles handpieces

Description

The **green Ivory Silk Line 2:1 fibre optic contra-angle, KaVo compatible**, is designed for professionals looking for a prophylaxis instrument that combines precision, comfort and high operating quality in every treatment.

The **2:1 reduction transmission** provides effective control during use, while the **fibre optic system** improves visibility of the working field, making the instrument suitable for procedures requiring accuracy and stability.

Designed with advanced microtechnology, this contra-angle delivers high performance and supports more efficient instrument management. The **removable head** allows different heads, both standard and reduction heads, to be used with a single contra-angle body, helping to optimise investment costs.

Compact head facilitates access to sensitive and hard-to-reach areas, improving operating control during prophylaxis procedures.

The high-purity glass light conductor reduces the refractive index and provides bright, uniform illumination without shadow areas, ensuring a clear working field.

Mechanical transmission components are designed with an extremely low tolerance threshold, transferring power from the micromotor without energy loss and without noise or vibration.

Elegant, precise and functional, the **green Ivory Silk Line 2:1 fibre optic contra-angle, KaVo compatible**, is a professional solution designed to improve efficiency, visibility and the quality of daily clinical work.

Technical features Green Ivory Silk Line 2:1 fiber optic contra-angle compatible Kavo:

Removable head	YES
Optical fiber	YES



Intensity of Light	Greater than 40,000 Lux
Transmission	2: 1
Rotor bearings	In Ceramics
Indications	Prophylaxis
Stop mechanism	Button
Type of Spray	Internal
Compatibility	Intramatic Universal
Rotation speed	20.000
Head Rotation	NO
Diameter of the Head	9.5mm
Head Height	11.6mm
Diameter of the Bur	2.334/2.350 mm
Length of the Bur	21.95mm
Weight	79gr
Autoclavable	YES
Type of Lubrication	Oil