



## Ivory coupling for KaVo turbines with LED light

Ivory Silk Line coupling for Kavo® Multiflex® turbines with LED light, 6-way

**Shipping expected in approximately 15 days**

**SKU:** C30LK

**Categories:** High-speed handpieces Couplings

### Description

---

#### Kavo Multiflex Dental Coupling – Ivory Silk Line C30LK, 6 Holes, LED, 360° Rotation, Ultra-Light 24g

The **Ivory Silk Line C30LK dental coupling** is designed to deliver optimal performance, ergonomic comfort, and long-lasting reliability. Fully **compatible with Kavo® Multiflex® connections**, it offers seamless integration with your existing turbine handpieces.

Its **360-degree rotation system** allows full freedom of movement, ensuring smooth handling and reducing wrist fatigue—even during extended procedures. At just **24g**, the C30LK is **ultra-lightweight**, improving balance and control without sacrificing durability.

Equipped with a **high-performance LED light**, the coupling delivers bright, focused illumination for over **50,000 hours**. This enhanced visibility improves accuracy and efficiency, especially in deep or hard-to-access treatment zones.

Built from premium materials, the C30LK coupling withstands daily use, mechanical stress, and sterilization cycles—making it a durable and trusted tool in any clinical setting.

Its **6-hole configuration** ensures optimal air and water flow for your turbine, while maintaining full compatibility with **Kavo Multiflex LED handpieces**.

Whether you're upgrading your existing equipment or adding a new coupling to your setup, the **Ivory Silk Line C30LK** offers exceptional value in terms of performance, comfort, and precision.

### Technical Features



|                    |                      |
|--------------------|----------------------|
| Rotation           | 360°                 |
| Illumination       | led                  |
| Compatibility      | Kavo® Multiflex®     |
| Connection         | 6 ways               |
| Intensity of light | 25.000 lux           |
| Voltage            | (vdc): LED / 3.3-3.8 |
| Autoclavabile      | No                   |
| Spray Regulation   | No                   |
| Weight             | 24 gr.               |