



Printed on 02/06/2025

<https://shop.tecnomeditalia.com/en/product/ivory-silk-line-1-1-fiber-optic-blue-contra-angle-spray-head-comp-kavo/>



Ivory Silk Line 1:1 fiber optic blue contra-angle, spray head comp. KaVo

Ivory Silk Line 1:1 fiber optic blue contra-angle for prophylaxis, Intramatic coupling, internal spray, Kavo compatible head

578,98 €

Available

SKU: SL411L

Categories: Professional Equipment

Description

Ivory Silk Line 1:1 fiber optic blue contra-angle compatible KaVo, spray head for Prophylaxis and 1: 1 transmission.

Like all the Ivory Prophylaxis line, it has been designed with the utmost care and the best of microtechnology to offer you excellent benefits. Thanks to its removable head you optimize the investment costs in instrumentation, since in a single contra angle you can apply different heads, both normal and reductive. In addition, the reduced size of the head allows access to the most sensitive and unreachable areas and the high degree of purity of the light conductor, made of vitreous material, reduces the refractive index and together with the vast field of irradiation, helps to guarantee an incomparable brightness and an operative field without zones of shade. Also, the mechanical transmission devices are designed with an extremely low tolerance threshold so that they can transmit the power developed by the micromotor without energy dispersion and without emitting noise or vibrations.

All this, accompanied by an impeccable and elegant design, make this contra-angle an extremely beautiful and indispensable piece for your work.

Technical features Ivory Silk Line 1:1 fiber optic blue contra-angle compatible KaVo:

Removable head	YES
Optical fiber	YES
Intensity of Light	Greater than 40,000 Lux
Transmission	1: 1
Rotor bearings	In Ceramics
Indications	Prophylaxis
Stop mechanism	Button
Type of Spray	Internal
Compatibility	Intramatic Universal
Rotation speed	40.000

Head Rotation	NO
Diameter of the Head	9.5mm
Head Height	11.6mm
Diameter of the Bur	2.334/2.350 mm
Length of the Bur	21.95mm
Weight	79gr
Autoclavable	YES
Type of Lubrication	Oil