



Ivory Silk Line 1:1 fiber optic blue contra-angle, spray head comp. KaVo

Ivory Silk Line 1:1 fiber optic blue contra-angle for prophylaxis, Intramatic coupling, internal spray, Kavo compatible head

Available

SKU: SL411L

Categories: Contra-Angles handpieces

Description

The **blue Ivory Silk Line 1:1 fibre optic contra-angle, KaVo compatible, with spray and removable head** is the ideal solution for professionals looking for a prophylaxis instrument that combines precision, operating comfort and effective illumination during clinical work.

Equipped with **fibre optics** and direct **1:1** transmission, it is designed to provide smooth, stable and comfortable use. Its careful construction and advanced microtechnology ensure reliability, ergonomics and high-quality movement during every procedure.

The **removable head** makes cleaning and maintenance easier, allowing different heads, both standard and reduction heads, to be used with a single contra-angle body. This feature helps optimise investment costs and makes instrument management more efficient.

Compact head facilitates access to sensitive and hard-to-reach areas, while the high-purity glass light conductor provides bright, uniform illumination without shadow areas. The result is a clear operating field and greater precision during treatment.

The high-precision mechanical transmission components, designed with an extremely low tolerance threshold, reduce vibrations, noise and energy loss. This ensures smooth, quiet and reliable operation over time.

The **blue Ivory Silk Line 1:1 fibre optic contra-angle, KaVo compatible, with spray and removable head** can be thermally decontaminated and sterilised in an autoclave up to **135°C**, offering hygiene, operating durability and safe use in daily practice.

Technical features Ivory Silk Line 1:1 fiber optic blue contra-angle compatible KaVo:

Removable head	YES
----------------	-----



Optical fiber	YES
Intensity of Light	40,000 Lux
Transmission	1: 1
Indications	Prophylaxis and restorative dental procedures
Stop mechanism	Button
Type of Spray	Internal
Compatibility	Intramatic Universal
Rotation speed	40.000
Head Rotation	NO
Diameter of the Head	9.5mm
Head Height	11.6mm
Diameter of the Bur	2.334/2.350 mm
Length of the Bur	9–34mm
Weight	79gr
Autoclavable	YES
Type of Lubrication	Oil