



## Ivory Silk Line 1:5 red contra-angle with spray

Ivory Silk Line 1:5 red multiplier contra-angle, Intramatic coupling, internal spray

**Available on request**

**SKU:** SL415C

**Categories:** Contra-Angles

### Description

The **red contra-angle Ivory Silk Line 1:5 blind with spray** is our 1:5 speed-increasing contra-angle without optical fibre, engineered for precision and freedom of movement. Ideal for **Restorative and Prosthetic Implantology**, it features a compact head that allows access to the most restricted areas.

Its **monoblock design** ensures easier cleaning, quieter operation and excellent handling. The **ceramic ball bearings** provide longer service life and reduced noise levels, guaranteeing smooth and consistent performance.

The **high-precision transmission system** minimises mechanical tolerances, allowing the micromotor's power to be transferred efficiently without vibration or energy loss. The reduced head size enhances visibility and control, especially in delicate treatment zones.

The Ivory Silk Line 1:5 red contra-angle can be **thermo-disinfected and sterilised in an autoclave up to 135°C**, ensuring hygiene, durability and consistent reliability.

### Technical features

Removable head	NO
Optical fiber	NO
Transmission	1:5
Rotor bearings	In Ceramics
Indications	Prosthetic Restoration and Restoration
Stop mechanism	Button
Type of Spray	Internal



Compatibility	Intramatic Universal
Rotation speed	200.000
Head Rotation	NO
Diameter of the Head	9.9mm
Head Height	14.5mm
Diameter of the Bur	1.59-1.60mm
Length of the Bur	10-25mm
Weight	82gr
Autoclavable	YES
Type of Lubrication	Oil