



Ivory Silk Line 1:5 red contra-angle with spray

Ivory Silk Line 1:5 red multiplier contra-angle, Intramatic coupling, internal spray

Available on request

SKU: SL415C

Categories: Contra-Angles

Description

The **red contra-angle Ivory Silk Line 1:5 blind with spray** is our 1:5 speed-increasing contra-angle without optical fibre, engineered for precision and freedom of movement. Ideal for **Restorative and Prosthetic Implantology**, it features a compact head that allows access to the most restricted areas.

Its **monoblock design** ensures easier cleaning, quieter operation and excellent handling. The **ceramic ball bearings**provide longer service life and reduced noise levels, guaranteeing smooth and consistent performance.

The **high-precision transmission system** minimises mechanical tolerances, allowing the micromotor's power to be transferred efficiently without vibration or energy loss. The reduced head size enhances visibility and control, especially in delicate treatment zones.

The Ivory Silk Line 1:5 red contra-angle can be **thermo-disinfected and sterilised in an autoclave up to 135°C**, ensuring hygiene, durability and consistent reliability.

Technical features

Removable head	NO
Optical fiber	NO
Transmission	1:5
Rotor bearings	In Ceramics
Indications	Prosthetic Restoration and Restoration
Stop mechanism	Button
Type of Spray	Internal



Intramatic Universal
200.000
NO
9.9mm
14.5mm
1.59-1.60mm
10-25mm
82gr
YES
Oil