



Ivory Silk Line led pneumatic micromotor, internal spray, 25,000 rpm

Ivory pneumatic micromotor. 6-way LED coupling, Intramatic. Internal spray, max. speed 25,000rpm. Reversing ring

Estimated shipping in 15 days

SKU: M714L

Categories: Air Micromotors

Description

The **Ivory Silk Line LED air micromotor 25,000 rpm with internal spray** proves that “micro” does not necessarily mean small.

Despite its compact size, the innovative vane rotor design delivers a **torque level comparable to an electric version**, while ensuring **greater reliability and reduced maintenance requirements**.

The integrated LED light provides **uniform illumination of the entire operating field**, while the speed can be easily adjusted up to 25,000 rpm via the control ring at the base. This allows practitioners to perform a wide range of procedures with **maximum precision and ergonomic comfort**.

The **stainless steel body** ensures long-term durability and enables **autoclave sterilisation up to 135°C**, meeting the highest hygiene and safety standards required in clinical environments.

To explore further advantages and review key features, including **demonstration videos and technical materials**, authorised dealers can access the dedicated area using their login credentials.

Technical features Ivory Silk Line led pneumatic micromotor 25.000 rpm

Type of Spray	Internal
Compatibility	6 ways
Light Source / Voltage	(vdc): LED / 3.3-3.8
Speed ??regulation	Yes
Reverse rotation	Yes
Air Consumption	(NL/min a 0.28 MPa): 50



Weight	130 gr
Maximum rotation per minute	25.000
Type of Lighting	LED
Power	Air
Autoclavable	Yes
Diameter	20mm
Type of Lubrication	Oil/Grease