



## Ivory Silk Line led pneumatic micromotor, internal spray, 25,000 rpm

Ivory pneumatic micromotor. 6-way LED coupling, Intramatic. Internal spray, max. speed 25,000rpm. Reversing ring

**Available on request**

**SKU:** M714L

**Categories:** Air Micromotors

### Description

The Ivory Silk Line led pneumatic micromotor 25.000 rpm, internal spray, makes that “micro” not always is synonymous with small!

Small in dimensions, light in weight and large in terms of performance, thanks to the innovative blade rotor, the M714L Ivory Silk Line Air Micromotor has a torque comparable to that of the electric version, although guaranteeing a greater reliability.

In addition, with its Led Light, capable of illuminating the whole field of work and a speed of up to 25,000 rpm that you can easily adjust from the ring placed at the base of it, you can comfortably perform any type of intervention.

Because its surface in steel guarantees a long durability and the safety of being able to sterilize it in an autoclave at 135 ° C all the times you need; knowing that this “small”, big engine will help you in your work for a very long time.

Technical features Ivory Silk Line led pneumatic micromotor 25.000 rpm

Type of Spray	Internal
Compatibility	6 ways
Light Source / Voltage	(vdc): LED / 3.3-3.8
Speed ??regulation	Yes
Reverse rotation	Yes
Air Consumption	(NL/min a 0.28 MPa): 50
Weight	130 gr



Maximum rotation per minute	25.000
Type of Lighting	LED
Power	Air
Autoclavable	Yes
Diameter	20mm
Type of Lubrication	Oil/Grease