




Printed on 02/06/2025

<https://shop.tecnomeditalia.com/en/product/ivory-silk-line-pneumatic-micromotor-blind-internal-spray-25000-rpm/>



Ivory Silk Line pneumatic micromotor blind, internal spray, 25,000 rpm

Ivory pneumatic micromotor. 4-way coupling, Intramatic. Internal spray, max. speed 25,000rpm. Reversing ring

222,20 €

Available

SKU: M714C

Categories: Professional Equipment

Description

The Ivory Silk Line pneumatic micromotor blind 25.000 rpm, internal spray, make that “micro” not always is synonymous with small!

Although of reduced dimensions, thanks to the innovative blade rotor, this Pneumatic Micromotor has a torque comparable to that of the electric version, guaranteeing a greater reliability. It is also ultralight and has a speed of up to 25,000 rpm that you can easily adjust from the ring placed at the base of it to perform most of the treatments.

Furthermore with its surface in steel of high durability, you can sterilize it in autoclave at 135 ° C all the times you need; knowing that this “small”, big engine will help you in your work for a very long time.

Technical features Ivory Silk Line pneumatic micromotor blind 25.000 rpm

Type of Spray	Internal
Compatibility	4 ways
Speed ??regulation	Yes
Reverse rotation	Yes
Air Consumption	(NL/min a 0.28 MPa): 50
Weight	110 gr
Maximum rotation per minute	25.000
Power	Air
Autoclavable	Yes
Diameter	20mm
Type of Lubrication	Oil/Grease