



KaVo PIEZOLED scaler hose compatible,1250mm,1.3kohm for KaVo E50S/TM

Scaler hose, 1250mm, KaVo PiezoLED compatible, 1,3 kohm, jumper with spray regulator, for KaVo E50S/TM - E70C/S/T - E80C - E80T - 1058

Available

SKU: PC152KEWG

Categories: Scalers

Description

Scaler hose compatible with KaVo PiezoLED, 1.3kohm resistor, Jumper, water regulation, length 1250mm. Fits models E50S/TM, E70C/S/T, E80C, E80T, 1058.