



## KaVo PIEZOLED scaler hose compatible, 1250mm, 1.3kohm for KaVo E50S/TM

Scaler hose, 1250mm, KaVo PiezoLED compatible, 1,3 kohm, jumper with spray regulator, for KaVo E50S/TM - E70C/S/T - E80C - E80T - 1058

**Available from 25/05/2026**

**SKU:** PC152KEWG

**Categories:** Scalers

### Description

---

Scaler hose compatible with KaVo PiezoLED, 1.3kohm resistor, Jumper, water regulation, length 1250mm. Fits models E50S/TM, E70C/S/T, E80C, E80T, 1058.