



Printed on 31/05/2025

<https://shop.tecnomeditalia.com/en/product/metasys-excom-hybrid-5-suction-system-for-3-5-dental-units/>



Metasys Excom Hybrid 5 suction system for 3/5 dental units

Metasys Excom Hybrid 5 suction system for 3/5 dental units, wet loop, with control unit and 180mb inverter

5.357,66 €

Available on request

SKU: 02010202

Categories: Hybrid wet ring

Description

Metasys Excom Hybrid 5 Suction system for 3/5 dental units.

Innovation and Power for Your Dental Practice

The METASYS EXCOM Hybrid suction system represents the cutting edge of technology for dental practices, combining dry and semi-wet suction in a single solution. Designed to ensure constant and reliable suction power, EXCOM Hybrid eliminates the need to choose between the two technologies, offering flexibility and high performance in any situation.

Key Features of the METASYS EXCOM Hybrid

- **Hybrid Technology:** EXCOM Hybrid integrates both dry and semi-wet suction functionality into a single device, adapting to the specific needs of the practice. This revolutionary combination simplifies installation and management of the suction system, making it versatile and easy to use.
- **Constant and Reliable Power:** With its advanced design, EXCOM Hybrid guarantees uniform suction power even during prolonged use and the most demanding conditions. This ensures a continuous, uninterrupted flow, enhancing the operational efficiency of the practice.
- **Innovative Design and Simplified Maintenance:** The system is designed to minimize maintenance interventions thanks to the use of advanced and durable materials. Installation is simple, and the quiet operation ensures a comfortable working environment for both the dentist and the patient.

Why Choose the EXCOM Hybrid Suction System from METASYS?

Choosing METASYS EXCOM Hybrid means investing in advanced technology that enhances the efficiency of your dental practice. With a unique combination of dry and semi-wet suction, you can offer your patients a comfortable experience while reducing treatment times and increasing the productivity of your team.

Advantages of the METASYS EXCOM Hybrid Suction System:

- **Versatility and Flexibility** – Suitable for various types of treatments thanks to its hybrid technology.
- **Energy Efficiency** – Reduced consumption and maximum suction power for continuous operation.
- **Guaranteed Reliability** – High-quality materials and innovative design for long-lasting durability.

Choose the EXCOM Hybrid by Metasys from Tecnomed Italia and discover a new level of efficiency and reliability in suction systems for dental practices. Optimize your daily work with the most advanced suction technology on the market, with the assurance and guarantee of Tecnomed Italia's after-sales service.

Technical features Metasys Excom Hybrid 5 Suction system for 3/5 dental units.

Type	Water ring
Dental units served	4 at 100%, 5 at 60%(4+1)
Control unit	yes
Own cabinet	No
Water drain	Forced
Noise level (db)	64
Amalgam recovery	
Power (Watt)	1500
Head (mmH2 O)	1835
Vacuum (mBar)	180
Flow rate (l/min)	2100
Power supply	230 Vac-50/60 Hz
Weight (Kg)	34
Dimensions (lpxh)mm	499 x 363 x 626
Warranty (months)	12 months
Certification	CE