



Rotor, W&H Alegra TE-95RM Led compatible, ceramic Myonic bearings

Compatible rotor for the **W&H Alegra TE-95RM LED+** high speed handpiece, supplied with **Myonic Torlon ceramic bearings** for precise and reliable technical maintenance.

Available on request

SKU: WT95RLK

Categories: Synea-Alegra

Description

Complete compatible rotor for the **W&H Alegra TE-95RM LED+** high speed handpiece, supplied with **Myonic Torlon ceramic bearing**.

Handpiece compatibility

- W&H Alegra TE-95RM LED+

Technical features

- Noise level <80dB
- Balancing <2g
- Eccentricity <0.15mm
- Supplied with Myonic Torlon ceramic bearings
- Dynamically balanced rotor
- Serial number identification
- Bur holding force >40 Newton
- 12-month warranty
- Complies with EN ISO 13485, EN ISO 10993-1, EN ISO 17665-1 and EN ISO 5349 standards