



## Sealing machine Termoseal 300, sealing 36 cm, continuous heating

Termoseal 300 sealing machine, sealing length 36 cm, width 1.5 cm, continuous heating

**Available**

**SKU:** SEA300

**Categories:** Packaging Equipment

### Description

---

Dental sealing machine Termoseal 300 is the electronic thermal sealing machine in continuous cycle and constant temperature by Tecnomed Italia

Characterized by a clean line and compact line, synonymous with robustness, reliability and ease of use.

The lever mechanism for welding is placed sideways; at the slightest pressure you can effortlessly obtain perfect seals for the packing of the instruments.

A built-in cutter allows you to cut the envelopes from a roll during the operation sealing easily and flexibly

Sealing machine Thermoseal 300 was conceived using the technology of current heating through a filament that becomes almost incandescent. A technique can lead to a high degree of wear and the upper protective canvas could burn, hole or tear.

Termoseal 300 is revolutionary: the heating of the welding element (an indestructible aluminum bar) is done through internal resistance that always maintains a constant temperature and adjustable by the operator.

This technology allows to perform thermal welding at repetition without wasting time and making the reliability of your seal up to three times higher than the older generation ones.

A special knob allows you to adjust the welding temperature up to 200°C based on the type of paper you are using (smooth or corrugated).

The on sight aluminum bar is indestructible and through internal resistance you can have a constant temperature.

The smooth surface allows easy cleaning increasing safety for operators and for the patient. With Thermoseal 300 the packaging operation are safe and fast: just lower with one hand the welding lever and



with the other hand slide the cutting lever.

The 15mm seal ensures a risk-free airtight closure.

**Supplied Dental sealing machine Termoseal 300**

- Thermal sealing machine
- n.2 Support rods
- n.1 Roll support rod
- Power cable

Features	Code SEA300
Weld width	15 mm
Weld length	360 mm
Roll support rod length	375 mm
Power	450 watt
Power supply	230 vac
Measurements (LxDxH)	500X260X200/260h
Weight	6.5 Kg
Warranty (months)	24
Certifications	CE