



Straight blue Ivory Silk Line 1:1 fiber optic, with spray, Intramatic

Straight blue Ivory Silk Line 1:1 fiber optic, Intramatic coupling, internal spray, maximum speed 40,000rpm

Available

SKU: SL211L

Categories: Straight Handpieces

Description

Ivory Neo Line Straight Handpiece Blue Intramatic Connection, Fibre Optic

The **Ivory Neo Line straight handpiece blue Intramatic connection fibre optic** combines flexibility, lightness and precision for professional dental applications. Its advanced design ensures effortless handling and superior control during any procedure.

Maximum flexibility and handling comfort.

The lightweight, balanced body allows smooth operation and reduces hand fatigue, ensuring comfort even during extended treatments. It adapts easily to different working needs while maintaining excellent control and precision.

Smooth, quiet and efficient transmission.

The mechanical transmission system is engineered with extremely low tolerances, ensuring optimal power transfer from the micromotor without energy or sound loss. The result is a **vibration-free**, **silent** and highly efficient performance.

High-brightness fibre optic.

Equipped with **integrated fibre optic lighting**, it provides bright, even illumination of the working area. The glass-based light conductor ensures high purity and reduced refraction, delivering **exceptional brightness and visibility** in every clinical situation.

Technical features Straight blue Ivory Silk Line Intramatic fiber optic



Type of Spray	Internal
Optical fiber	Yes
Intensity of light	Up to 40.000 Lux
Connection	Intramatic Universal
Transmission	1:1
Drill Diameter	2,344/2,350 mm
Drill length	21,95/44,50 mm
Weight	95 gr.
Maximum rotation per minute	40.000 rpm
Connection	Intramatic Universal
Autoclavable	Yes
Type of Lubrication	Oil