



Printed on 02/06/2025

<https://shop.tecnomeditalia.com/en/product/tecnomed-dental-wall-x-ray-unit-dc-60-70kv-lcd-arm-1730mm/>



## Tecnomed dental wall X-ray unit, DC 60/70kv, LCD, arm 1730mm

Tecnomed dental wall X-ray unit, DC 60/70kv, with LCD handheld and DAP value, wireless, arm extension 1730mm

**3.635,28 €**

**Available on request**

**SKU:** DE73RX4

**Categories:** X-ray machines

### Description

The intraoral X-ray unit wall mounted DC 60/70kv 1730mm arm is the ideal solution for dental practices seeking precision and safety. With the new DE73RX Tim-x configuration, this device combines advanced performance with an easy-to-install wall-mounted design, ensuring high-quality imaging with reduced exposure times.

Equipped with a 0.3 mm micro focal spot, the intraoral X-ray system delivers highly detailed radiographic images, compatible with films, digital sensors, and phosphor plates. The cutting-edge wireless LCD TIM-X remote control allows users to adjust exposure parameters such as kilovolts (kV), milliamperes (mA), and exposure time (ms) with total ease and safety. The pre-set R10 exposure scale can be customized according to the specific needs of the user, ensuring flexibility in operation.

#### Key Features:

- **High-precision imaging:** The 0.3 mm micro focal spot captures every detail with exceptional clarity, essential for accurate diagnoses.
- **Wireless control:** The state-of-the-art TIM-X remote control enables users to manage exposure settings remotely, providing both convenience and safety.
- **Smooth positioning:** The lightweight monoblock design allows for effortless positioning, eliminating vibrations and ensuring stability during radiographic exposures.
- **Customizable exposure settings:** The pre-set R10 exposure scale can be tailored to individual preferences, allowing for greater adaptability.

#### Suitable for:

This intraoral X-ray unit is designed for dental practices that prioritize reliable, cutting-edge imaging technology. It is ideal for professionals seeking high-quality radiographs with reduced radiation exposure for both patients and staff.

#### Technical Specifications:

- **Installation:** Wall-mounted
- **Extension:** 173 cm
- **Focal spot size:** 0.3 mm
- **kV:** 60/70
- **Anodic current:** 4/6.5 mA
- **Filtration:** 2 mm AL
- **Exposure control:** Wireless
- **Exposure time:** 0.020 – 1 sec
- **Cone diameter:** 6 cm
- **Power supply:** 230V  $\pm$  10%
- **Warranty:** 24 months

This advanced device combines innovation, safety, and ease of use, delivering high-quality radiographic images with exceptional precision and reliability.

**Technical features intraoral X-ray unit wall mounted DC 60/70kv 1730mm arm**

Mounting	wall
Extension	cm 173
Focal spot	0,3 mm
kV	60/70
Anodic current	4/6,5 mA
filtration mm	2 AL
X-ray control	Wireless
Exposure time	0,020 – 1 sec
Cone diameter	6 cm
Power supply	230V $\pm$ 10%
Warranty	24 months