



## Tecnomed dental wall X-ray unit, DC 60/70kv, LCD, arm 2130mm



Tecnomed dental wall X-ray unit, DC 60/70kv, with LCD handheld and DAP value, wireless, arm extension 2130mm

**Available on request**

**SKU:** DE73RX

**Categories:** DC Technology

### Description

---

#### **Intraoral X-ray Wall-Mounted DC 60/70kV 2130mm – Precision and Full Control with TIM-X Handset**

The **intraoral X-ray wall-mounted DC 60/70kV 2130mm** system delivers outstanding image quality with precise, safe exposure management. Its DC technology and advanced wireless TIM-X handset ensure optimal diagnostic performance and consistent radiation control.

#### **Wireless control and real-time DAP monitoring.**

The TIM-X handset enables full remote adjustment of exposure parameters – kilovoltage (kV), milliamperage (mA) and exposure time (ms) – for effortless, ergonomic operation. Real-time DAP value display ensures continuous monitoring of radiation dose and enhanced patient safety.

#### **0.3mm focal spot for high-definition images.**

Equipped with a Toshiba D-045 OX/70-4 OX/70-3 tube and a 0.3mm focal spot (IEC 336), the unit produces ultra-sharp radiographs using any type of film or digital sensor. DC current technology minimises exposure time and maximises image clarity.

#### **Stable, lightweight and adaptable design.**

The dual pantograph arm is lightweight, self-balancing and easy to position, ensuring smooth handling in any clinical setting. The TECNOXRAY DC unit supports both conventional and RVG modes, offering full flexibility for professional dental diagnostics.

#### **Technical features intraoral x-ray unit wall DC 213cm**



|                |                |
|----------------|----------------|
| Mounting       | wall           |
| Extension      | 213 cm         |
| Focal spot     | 0,3 mm         |
| kV             | 60/70          |
| Anodic current | 4/6,5 mA       |
| filtration mm  | 2 AL           |
| X-ray control  | Wireless       |
| Exposure time  | 0,020 – 1 sec  |
| Cone diameter  | 6 cm           |
| Power supply   | 230V $\pm$ 10% |
| Warranty       | 24 months      |