

Tecnomed dental wall X-ray unit, DC 60/70kv, LCD, arm 2430mm



Tecnomed dental wall-mounted X-ray unit, DC 60/70kv, with LCD handheld and DAP value, wireless, arm extension 2430mm

Available on request

SKU: DE73RX1

Categories: DC Technology

Description

Intraoral X-ray Wall-Mounted DC 60/70kV 2430mm – Precision and Full Control with TIM-X Handset

The **intraoral X-ray wall-mounted DC 60/70kV 2430mm** system delivers outstanding image quality with precise, safe exposure management. Its DC technology and advanced wireless TIM-X handset ensure optimal diagnostic performance and consistent radiation control.

Wireless control and real-time DAP monitoring.

The TIM-X handset enables full remote adjustment of exposure parameters – kilovoltage (kV), milliamperage (mA) and exposure time (ms) – for effortless, ergonomic operation. Real-time DAP value display ensures continuous monitoring of radiation dose and enhanced patient safety.

0.3mm focal spot for high-definition images.

Equipped with a Toshiba D-045 OX/70-4 OX/70-3 tube and a 0.3mm focal spot (IEC 336), the unit produces ultra-sharp radiographs using any type of film or digital sensor. DC current technology minimises exposure time and maximises image clarity.

Stable, lightweight and adaptable design.

The dual pantograph arm is lightweight, self-balancing and easy to position, ensuring smooth handling in any clinical setting. The TECNOXRAY DC unit supports both conventional and RVG modes, offering full flexibility for professional dental diagnostics.

Technical features intraoral X-ray unit wall mounted DC 2430mm.



| | |
|----------------|----------------|
| Mounting | wall |
| Extension | 243 cm |
| Focal spot | 0,3 mm |
| kV | 60/70 |
| Anodic current | 4/6,5 mA |
| filtration mm | 2 AL |
| X-ray control | Wireless |
| Exposure time | 0,020 – 1 sec |
| Cone diameter | 6 cm |
| Power supply | 230V \pm 10% |
| Warranty | 24 months |