



## Tecnomed dental wall X-ray unit, DC 60/70kv, LCD, arm 2430mm

Tecnomed dental wall-mounted X-ray unit, DC 60/70kv, with LCD handheld and DAP value, wireless, arm extension 2430mm

**Available on request**

**SKU:** DE73RX1

**Categories:** X-ray machines

### Description

The intraoral X-ray unit wall mounted DC 2430mm arm is the ideal solution for dental practices seeking precision and safety. With the new DE73RX Tim-x configuration, this device combines advanced performance with an easy-to-install wall-mounted design, ensuring high-quality imaging with reduced exposure times.

Equipped with a 0.3 mm micro focal spot, the intraoral X-ray system delivers highly detailed radiographic images, compatible with films, digital sensors, and phosphor plates. The cutting-edge wireless LCD TIM-X remote control allows users to adjust exposure parameters such as kilovolts (kV), milliamperes (mA), and exposure time (ms) with total ease and safety. The pre-set R10 exposure scale can be customized according to the specific needs of the user, ensuring flexibility in operation.

#### Key Features:

- High-precision imaging: The 0.3 mm micro focal spot captures every detail with exceptional clarity, essential for accurate diagnoses.
- Wireless control: The state-of-the-art TIM-X remote control enables users to manage exposure settings remotely, providing both convenience and safety.
- Smooth positioning: The lightweight monoblock design allows for effortless positioning, eliminating vibrations and ensuring stability during radiographic exposures.
- Customizable exposure settings: The pre-set R10 exposure scale can be tailored to individual preferences, allowing for greater adaptability.

#### Suitable for:

This intraoral X-ray unit is designed for dental practices that prioritize reliable, cutting-edge imaging technology. It is ideal for professionals seeking high-quality radiographs with reduced radiation exposure for



both patients and staff.

This advanced device combines innovation, safety, and ease of use, delivering high-quality radiographic images with exceptional precision and reliability.

**Technical features intraoral X-ray unit wall mounted DC 2430mm.**

Mounting	wall
Extension	243 cm
Focal spot	0,3 mm
kV	60/70
Anodic current	4/6,5 mA
filtration mm	2 AL
X-ray control	Wireless
Exposure time	0,020 – 1 sec
Cone diameter	6 cm
Power supply	230V $\pm$ 10%
Warranty	24 months