



Tecnostill electric distiller, PVC and stainless steel, 1.5l/h

Tecnostill electric distiller, PVC exterior and stainless steel tank, distils 1.5l/h complete with accessories

Available

SKU: DEA05Q

Categories: Distillers

Description

Tecnostil water distiller – Fast production of pure distilled water for medical and dental use

The **Tecnostil** water distiller produces pure distilled water through boiling and forced recondensation. Designed for medical and dental practices, it ensures a steady and safe supply of impurity-free water.

Reliable performance and ease of use

With an output of up to **1.5 litres of distilled water per hour**, Tecnostil guarantees instant availability of sterile water for clinical procedures. Its **automatic shut-off timer** activates when the water runs out, preventing waste and protecting the unit.

Durable build and functional design

The **white PVC exterior** provides a sleek, easy-to-clean finish, while the **stainless steel inner tank** ensures hygiene, corrosion resistance and long-lasting durability.

Simple installation and minimal maintenance

Tecnostil is ready to use right away: just plug it in to start producing distilled water—no technical setup or adjustments required.

Composition Tecnostill electric distiller pvc-inox DEA05Q:

- Distiller
- Tank
- Tank cap
- Coal filter
- Citric acid
- Power cable

Data sheet Tecnostil Distillers



Article Code	DEA05Q	DEA05QX
Shutdown safety thermostat	160 °C Automatic water run-out	160 °C Automatic water or time run-out
Litres distillation capacity per hour	1	1
External material	White PVC	Inox
Tub material	Inox	Inox
Temperature regulation		•
Display		•
Power	230 vac	230 vac
Size with tank mm	375x385	375x385
Weight Kg.	3,5	3,5
Warranty	24 months	24 months