



Tecnostill electric distiller, PVC and stainless steel, 1.5l/h

Tecnostill electric distiller, PVC exterior and stainless steel tank, distills 1.5l/h complete with accessories

Available

SKU: DEA05Q

Categories: Water distillers

Description

Tecnostill electric distiller pvc-inox is the new Tecnomed Italia distiller that generates boiling distilled water thanks to forced condensation.

Simple both the installation and the use, can produce 1,5 liters of pure distilled water in an hour.

Just fill the tank with tap water and turn on the network switch. With Tecnostil any problem with using non-pure water will be eliminated.

The distilled water produced in equipment such as the autoclave will avoid problems with the electrovalves or internal ducts. The instruments will be brilliant and free of limestone residue.

No more wasting time buying bulky containers of distilled water.

Tecnostil is available in white or stainless version with display panel for temperature control and shutdown time.

Resistant stainless steel condensation boiler with maximum water signal. The tank is extremely durable and has a capacity of 4 liters and is equipped with an airtight locking cap.

Automatic shutdown at the end of the cycle. Connector with power button on the back.

Composition Tecnostill electric distiller pvc-inox DEA05Q:

- Distiller
- Tank
- Tank cap
- Coal filter
- Citric acid



- Power cable

Data sheet Tecnostil Distillers

Article Code	DEA05Q	DEA05QX
Shutdown safety thermostat	160 °C Automatic water run-out	160 °C Automatic water or time run-out
Litres distillation capacity per hour	1	1
External material	White PVC	Inox
Tub material	Inox	Inox
Temperature regulation		•
Display		•
Power	230 vac	230 vac
Size with tank mm	375x385	375x385
Weight Kg.	3,5	3,5
Warranty	24 months	24 months