



Ivory pneumatic micromotor, non-optic, spray, 25,000 rpm. REFURBISHED

Ivory pneumatic micromotor. 4-way coupling, Intramatic. Internal spray, max. speed 25,000rpm. Reversing ring. **REFURBISHED ONLY 13 PIECES AVAILABLES**

Available

SKU: OFOUT102

Categories: Outlet

Description

Ivory Silk Line pneumatic micromotor blind 25.000 rpm – **REFURBISHED ONLY 13 PIECES AVAILABLES.**

The **Ivory Silk Line pneumatic micromotor (blind version) 25.000 rpm with internal spray** is designed to ensure reliable performance and operational continuity in dental applications.

Featuring a next-generation vane rotor, it delivers **torque levels comparable to electric micromotors**, while offering **enhanced reliability and simplified maintenance**, making it particularly suitable for distributors and dealers.

Its compact design and lightweight construction provide **excellent handling and operator comfort**, while the speed can be adjusted up to **25,000 rpm via the control ring at the base**, allowing precise control across a wide range of clinical procedures.

The **high-strength stainless steel body** ensures long-term durability and allows **autoclave sterilisation up to 135°C**, in compliance with the highest hygiene standards required in the dental field.

This micromotor represents a **reliable, versatile and long-lasting solution**, ideal for inclusion in product portfolios aimed at dental professionals and practices.

Technical features Ivory Silk Line pneumatic micromotor blind 25.000 rpm

Type of Spray	Internal
Compatibility	4 ways
Speed ??regulation	Yes
Reverse rotation	Yes



Air Consumption	(NL/min a 0.28 MPa): 50
Weight	110 gr
Maximum rotation per minute	25.000
Power	Air
Autoclavable	Yes
Diameter	20mm
Type of Lubrication	Oil/Grease