

## HD-7H DTE-Woodpecker handpiece for scaling unit, Satelec compatible



White handpiece for Woodpecker power scaling unit, Satelec compatible

**Available from 11/05/2026**

**SKU:** M17S

**Categories:** Scaler Handpieces

### Description

---

#### **Piezoelectric Scaler Handpiece – HD-7H DTE by Woodpecker, Satelec Compatible, Autoclavable**

The **HD-7H scaler handpiece by DTE – Woodpecker** is a high-quality piezoelectric instrument designed for efficient scaling procedures and long-term clinical reliability. Crafted for precision and durability, this handpiece is **fully autoclavable**, maintaining its performance even under high temperatures and pressure without cracking or deforming.

Thanks to its **lightweight and ergonomic design**, the HD-7H fits comfortably in the hand, helping reduce operator fatigue during long sessions. Its smooth, contoured body allows for a secure grip and accurate movements, making it a valuable tool for hygienists and dental professionals who prioritize comfort and control.

The handpiece is **compatible with Satelec-style connection systems** and inserts, offering seamless integration into most dental units and with commonly used ultrasonic tips. This versatility makes it ideal for scaling, periodontal, and endodontic procedures.

Built with high-quality materials and excellent internal sealing, the HD-7H ensures both clinical safety and long-lasting performance. It's resistant to daily sterilization cycles and mechanical stress, making it a trusted component in any modern dental practice.

Whether you're replacing an existing handpiece or expanding your equipment lineup, the **HD-7H DTE-Woodpecker handpiece** offers a reliable, affordable, and professional-grade solution for ultrasonic scaling.

Technical features.



Version	Scaler handpiece
Tip compatibility	Satelec®
Coupling compatibility	Satelec®
Color handpiece	White
Optic fibre	No
Light intensity (lux)	/
Ultrasonic frequency	28KHz +/- 3KHz
Ultrasonic transducer type	Ultrasonic
Dimensions (lxØ mm)	117 x 20
Handpiece weight (g)	58
Cord length (meters)	/
Autoclavable	Yes
Warranty	12 months
CE	0197